

Effective September 1, 2019

Visit our website for the most current information

NIBCO® PressACR FITTINGS



PC9600-2 Fitting Reducer (Ftg x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9600-2	3/8 x 1/4	\$ 31.42	.02	418418	10	150	9600
PC9600-2	1/2 x 3/8	37.76	.03	418425	10	150	9600
PC9600-2	5/8 x 3/8	34.90	.04	418432	10	150	9600
PC9600-2	5/8 x 1/2	38.78	.04	418449	10	150	9600
PC9600-2	3/4 x 5/8	40.75	.09	413741	10	150	7200
PC9600-2	7/8 x 1/2	40.46	.10	418456	10	150	9600
PC9600-2	7/8 x 5/8	38.35	.09	413765	10	150	9600
PC9600-2	7/8 x 3/4	42.60	.11	413758	10	150	9600
PC9600-2	1 1/8 x 7/8	68.72	.15	413772	10	150	9600
PC9600-2	1 3/8 x 7/8	75.60	.18	413796	5	50	4000
PC9600-2	1 3/8 x 1 1/8	78.25	.18	413789	1	50	2400



PC9600-R Reducing Coupling (P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9600-R	5/16 x 1/4	\$ 13.37	.01	418319	10	150	9600
PC9600-R	3/8 x 1/4	22.50	.01	418326	10	150	9600
PC9600-R	5/8 x 1/4	26.49	.01	418357	10	150	9600
PC9600-R	5/8 x 3/8	28.02	.01	418364	10	150	9600
PC9600-R	5/8 x 1/2	29.89	.01	418371	10	150	9600
PC9600-R	3/4 x 5/8	31.71	.10	413666	10	150	9600
PC9600-R	7/8 x 1/2	34.61	.10	418395	10	150	9600
PC9600-R	7/8 x 5/8	38.66	.12	413673	10	150	9600
PC9600-R	7/8 x 3/4	46.59	.13	413680	10	150	7200
PC9600-R	1 1/8 x 1/2	52.20	.14	418401	10	150	9600
PC9600-R	1 1/8 x 5/8	54.02	.14	413697	10	100	4800
PC9600-R	1 1/8 x 3/4	46.95	.17	413703	10	100	6400
PC9600-R	1 1/8 x 7/8	56.16	.18	413710	5	100	8000
PC9600-R	1 3/8 x 7/8	60.41	.25	413734	5	100	6400
PC9600-R	1 3/8 x 1 1/8	65.30	.23	413727	1	50	4000



PC9600-DS Coupling (P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9600-DS	1/4	\$ 8.53	.01	418289	10	250	16000
PC9600-DS	5/16	10.09	.01	418296	10	250	16000
PC9600-DS	3/8	11.62	.01	418302	10	250	16000
PC9600-DS	1/2	14.22	.05	418272	10	250	16000
PC9600-DS	5/8	18.47	.08	413611	10	250	16000
PC9600-DS	3/4	24.93	.11	413628	10	250	12000
PC9600-DS	7/8	27.73	.16	413635	10	150	7200
PC9600-DS	1 1/8	39.90	.20	413642	5	150	5400
PC9600-DS	1 3/8	47.61	.27	413659	1	30	1920



PC9601 Repair Coupling (P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9601	1/4	\$ 13.58	.01	418463	10	250	1600
PC9601	5/16	14.95	.01	427663	10	250	1600
PC9601	3/8	16.65	.01	418470	10	250	1600
PC9601	1/2	19.20	.05	418487	10	250	1600
PC9601	5/8	24.74	.08	413802	10	250	1600
PC9601	3/4	33.39	.11	413819	10	250	12000
PC9601	7/8	37.42	.16	413826	10	150	5400
PC9601	1 1/8	54.39	.19	413833	5	150	5400
PC9601	1 3/8	73.71	.27	413840	1	30	1440

NIBCO®
AHEAD OF THE FLOW®

* All fittings must be ordered in incremental bag quantities.

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
ELKHART, IN 46516-4740
USA

DOMESTIC CUSTOMER SERVICE
PHONE: 800.234.0227
FAX: 800.234.0557

TECHNICAL SERVICE
PHONE: 888.446.4226
FAX: 888.336.4226

INTERNATIONAL OFFICE
PHONE: +1/574.295.3327
FAX: +1/574.295.3455



PC9606-LT 45° Elbow (P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9606-LT	1/4	\$ 32.56	.01	418166	10	200	9600
PC9606-LT	5/16	36.17	.01	418173	10	200	9600
PC9606-LT	3/8	40.19	.01	418180	10	200	9600
PC9606-LT	1/2	44.57	.06	418159	10	200	12800
PC9606-LT	5/8	46.27	.09	413468	10	200	9600
PC9606-LT	3/4	56.33	.15	413475	10	200	9600
PC9606-LT	7/8	57.38	.18	413482	10	150	7200
PC9606-LT	1½	71.86	.25	413499	5	100	4800
PC9606-LT	1¾	95.67	.40	413505	1	50	2400



PC9607-LT 90° Elbow (P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9607-LT	1/4	\$ 20.73	.01	418081	10	150	9600
PC9607-LT	5/16	23.21	.01	418098	10	150	9600
PC9607-LT	3/8	29.99	.01	418104	10	150	9600
PC9607-LT	1/2	33.27	.08	418074	10	150	9600
PC9607-LT	5/8	34.53	.11	413369	10	150	9600
PC9607-LT	3/4	42.04	.17	413376	10	150	7200
PC9607-LT	7/8	42.82	.22	413383	10	150	7200
PC9607-LT	1½	53.63	.33	413390	5	100	3600
PC9607-LT	1¾	71.40	.53	413406	1	25	1200



PC9607-2-LT 90° Elbow (Ftg x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9607-2-LT	1/4	\$ 24.61	.01	418128	10	150	9600
PC9607-2-LT	3/8	41.02	.01	418135	10	150	9600
PC9607-2-LT	5/16	43.07	.01	418142	10	150	9600
PC9607-2-LT	1/2	44.30	.08	418111	10	150	9600
PC9607-2-LT	5/8	45.57	.11	413413	10	150	7200
PC9607-2-LT	3/4	53.07	.17	413420	10	150	7200
PC9607-2-LT	7/8	53.85	.22	413437	10	150	7200
PC9607-2-LT	1½	64.67	.32	413444	5	100	4800
PC9607-2-LT	1¾	82.43	.49	413451	1	25	1200



PC9611 Tee (P x P x P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9611	1/4	\$ 38.73	.01	418203	10	200	7200
PC9611	5/16	47.34	.01	418227	10	200	7200
PC9611	3/8	43.04	.01	418210	10	200	7200
PC9611	1/2	49.70	.11	418197	10	200	12800
PC9611	5/8	52.05	.18	413512	10	100	3600
PC9611	3/4	63.04	.34	413529	10	200	9600
PC9611	7/8	63.52	.32	413536	10	100	3600
PC9611	1½	80.49	.48	413543	5	50	1800
PC9611	1¾	106.25	.76	413550	1	25	1200



PC9649 Y Joint (FTG x FTG)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9649	3/8	\$ 14.46	.20	430618	2	40	240
PC9649	1/2	20.32	.31	430625	2	40	240
PC9649	5/8	28.75	.51	430632	2	30	180
PC9649	3/4	35.67	.67	430649	2	30	180
PC9649	7/8	55.75	1.02	430656	2	24	144
PC9649	1½	78.18	1.70	430663	2	12	72



PC9617 Tube Cap (P)

Fig. No.	Size (OD)	List Price	Unit Wt.	UPC 039923-	Packaging		
					Bag	Case	Pallet
PC9617	1/4	\$ 10.52	.01	418241	10	500	24000
PC9617	5/16	10.77	.01	418258	10	500	24000
PC9617	3/8	17.52	.01	418265	10	500	24000
PC9617	1/2	20.95	.03	418234	10	500	32000
PC9617	5/8	21.87	.05	413567	10	400	19200
PC9617	3/4	27.85	.07	413574	10	500	24000
PC9617	7/8	27.63	.09	413581	10	400	19200
PC9617	1½	31.08	.13	413598	5	200	16000
PC9617	1¾	39.00	.17	413604	1	100	4800



PRESSACR DEPTH TOOL

Fig. No.	List Price	Unit Wt.	UPC 039923-	Packaging		
				Bag	Case	Pallet
K700003RPC	\$ 7.48	.15	247438	1	16	2400



PRESSACR CRIMP GAUGE

Fig. No.	List Price	Unit Wt.	UPC 039923-	Packaging		
				Bag	Case	Pallet
K700005RPC	\$ 48.60	.35	433251	1	100	5000



HNBR Seal (leak detection)

Fig. No.	Size	List Price†	UPC 039923-
T048081 PP	5/16	1.88	407351
T048082 PP	3/8	1.88	407368
T048084 PP	1/2	1.88	407375
T048084 PP	5/8	2.02	407382
T048085 PP	3/4	2.02	407399
T048086 PP	7/8	2.02	407405
T048087 PP	1½	2.38	407412
T048088 PP	1¾	2.38	407429

† List prices for seals are per each and should be ordered in increments of 1.

NIBCO pres^system[®]

TOOLS AND ACCESSORIES

PCR-20M

1/4" thru 1 3/8" OD

MATERIAL LIST

MODEL NO.	DESCRIPTION	LBS.	LIST PRICE	UPC 039923-
PCR-20M	Mini Pressing Tool, 2 - 18V, 1.3 Ah Lithium-ion batteries, 110V charger & case (NO jaws)	11.00	\$ 3,060.44	417305
PCR-14M	1/4" OD Jaw	2.80	255.68	427618
PCR-516M	5/16" OD Jaw	2.81	255.68	427625
PCR-38M	3/8" OD Jaw	2.80	255.68	427632
PCR-12M	1/2" OD Jaw	2.89	255.68	430359
PCR-34M	3/4" OD Jaw	2.99	306.46	430366
PCR-1M	5/8" OD Jaw	3.06	255.68	417107
PCR-2M	7/8" OD Jaw	3.61	306.46	417114
PCR-3M	1 1/8" OD Jaw	3.79	467.94	417121
PCR-138M	1 3/8" OD Jaw for PC280	4.40	467.94	431615



PCR-20M
Mini Pressing Tool



**14M, 516M, 38M, 12M,
34M, 1M, 2M and 3M**
Mini Pressing Jaw

PCR-20M FEATURES

TOOLS

Light weight

PCR-20M Mini: 3.7 lbs. (without jaw)

Easy to handle / simple design

Jaws rotate 350°

No calibration necessary

No complicated switches or controls

Mini: Ergonomic compact design is easy to use in tight spaces

Interruptible crimp cycle

Safety feature prevents injuries

Can begin crimp, stop to align and level fitting / tube, and complete crimp

Battery

Can be changed during crimp cycle

Lithium-ion has short charging cycle and larger capacity

- PC-4ML: 15 minute recharge time
- PC-7L: 22 minute recharge time

AC Power Adapter

Converts the tool to electric power

Allows continuous use

Service light

Illuminates at 10,000 cycles

Tool will not stop operating when light illuminates

- RED indicates battery charge status, service intervals, tool functions & faults
- WHITE illuminates the work area

Hydraulic Pressure Check (HPC)

An audible warning signal sounds if adequate working pressure is not achieved

WARNING: Cancer and Reproductive Harm –
www.P65Warnings.ca.gov.

NIBCO[®]
AHEAD OF THE FLOW[®]

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
ELKHART, IN 46516-4740
USA

DOMESTIC CUSTOMER SERVICE
PHONE: 800.234.0227
FAX: 800.234.0557

TECHNICAL SERVICE
PHONE: 888.446.4226
FAX: 888.336.4226

INTERNATIONAL OFFICE
PHONE: +1/574.295.3327
FAX: +1/574.295.3455