

BRONZE & IRON
Y-STRAINERS

STR-1120

Effective November 9, 2020 • Supercedes STR-0320 of March 30, 2020



List Prices subject to change without notice
Visit our website for the most current information.

BRONZE Y-STRAINER — SOLDER END W/PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
S-221-A Class 125 20 Mesh Screen w/Plug	List Price	N/A	N/A	\$ 70.36	\$ 83.78	\$ 117.20	\$ 171.00	\$ 197.00	\$ 318.30	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279927	279934	279941	279958	279965	279972	—	—
S-222-A Class 125 Perforated Stainless Steel w/Plug	List Price	N/A	N/A	\$ 80.43	\$ 93.74	\$ 127.30	\$ 190.50	\$ 216.50	\$ 352.90	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280091	280107	280169	280176	280183	280190	—	—



BRONZE Y-STRAINER — SOLDER END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
S-221-B Class 125 20 Mesh Screen w/Solid Cap	List Price	N/A	N/A	\$ 70.36	\$ 83.78	\$ 118.30	\$ 168.80	\$ 195.90	\$ 316.00	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279989	279996	280008	280060	280077	280084	—	—
S-222-B Class 125 Perforated Stainless Steel w/Solid Cap	List Price	N/A	N/A	\$ 75.99	\$ 89.30	\$ 125.10	\$ 185.10	\$ 208.90	\$ 343.10	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280206	280213	280251	280268	280275	280282	—	—



BRONZE Y-STRAINER — THREADED END W/ PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-221-A Class 125 20 Mesh Screen w/Plug	List Price	\$ 68.09	\$ 68.09	\$ 68.09	\$ 92.66	\$ 118.30	\$ 165.20	\$ 198.10	\$ 340.90	\$ 742.00	\$ 1,013.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.96
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280299	280305	280312	280350	280367	280374	280381	280398	280442	280459
T-222-A Class 125 Perforated Stainless Steel w/Plug	List Price	\$ 70.36	\$ 70.36	\$ 70.36	\$ 99.37	\$ 126.10	\$ 178.60	\$ 210.00	\$ 364.80	\$ 794.00	\$ 1,085.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280619	280626	280633	280640	280657	280664	280671	280688	280695	280701

WARNING: Cancer and Reproductive Harm – www.P65Warnings.ca.gov.

NIBCO
AHEAD OF THE FLOW®

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
ELKHART, IN 46516-4740
USA

DOMESTIC CUSTOMER SERVICE
PHONE: 800.234.0227
FAX: 800.234.0557

TECHNICAL SERVICE
PHONE: 888.446.4226
FAX: 888.336.4226

INTERNATIONAL OFFICE
PHONE: +1/574.295.3327
FAX: +1/574.295.3455



BRONZE Y-STRAINER — THREADED END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-221-B Class 125 20 Mesh Screen w/Solid Cap	List Price	\$ 64.73	\$ 64.73	\$ 64.73	\$ 89.30	\$ 117.20	\$ 163.10	\$ 195.90	\$ 336.60	\$ 735.00	\$ 1,003.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280466	280473	280480	280497	280541	280558	280565	280572	280596	280602

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-222-B Class 125 Perforated Stainless Steel w/Solid Cap	List Price	\$ 68.09	\$ 68.09	\$ 68.09	\$ 96.01	\$ 120.50	\$ 171.00	\$ 202.40	\$ 349.60	\$ 765.00	\$ 1,037.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280848	280855	280862	280879	280886	280893	280909	281029	281036	281043



IRON Y-STRAINER — THREADED END

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-751-A Class 250 20 Mesh Screen w/Plug	List Price	\$ 26.73	\$ 26.73	\$ 26.73	\$ 39.41	\$ 52.07	\$ 67.65	\$ 93.52	\$ 142.80	\$ 283.60	\$ 389.70
	Unit Wgt.	1.39	1.39	1.39	2.20	3.08	5.06	7.70	12.54	24.42	29.26
	Case Qty.	10	10	10	10	8	6	4	3	1	1
	UPC 039923-	308498	308511	308535	308559	308573	308580	308597	308610	308634	308658



IRON Y-STRAINER — FLANGED

Fig. No.	Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
F-721-A Class 125 Perforated Screen w/Plug	List Price	\$ 295.50	\$ 321.50	\$ 376.70	\$ 571.00	\$ 1,039.00	\$ 1,289.00	\$ 2,281.00	\$ 4,225.00	\$ 6,030.00
	Unit Wgt.	18.04	32.56	37.84	67.10	94.60	136.62	270.60	374	605
	Case Qty.	1	1	1	1	1	1	1	1	1
	UPC 039923-	308672	308696	308702	308719	308733	308757	308771	308795	308801




IRON Y-STRAINER — FLANGED

Fig. No.	Size	14"	16"
F-721-A Class 125 Perforated Screen w/Plug	List Price	\$ 13,077.00	\$ 18,427.00
	Box Qty	10	10
	Unit Wgt.	863	1380
	Case Qty.	1	1
	UPC 039923-	310415	310422

WARNING: Cancer and Reproductive Harm – www.P65Warnings.ca.gov.

BRONZE REPLACEMENT PARTS



20 Mesh Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 20.67	\$ 20.67	\$ 20.67	\$ 20.67	\$ 24.69	\$ 30.20	\$ 34.31	\$ 59.21	\$ 26.20	\$ 52.17
Part Number	T066957PP	T066957PP	T066957PP	T066958PP	T066959PP	T066960PP	T066961PP	T066962PP	T066963PP	T066964PP



Perforated Stainless Steel Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 20.67	\$ 20.67	\$ 20.67	\$ 19.27	\$ 23.81	\$ 23.38	\$ 28.79	\$ 37.13	\$ 52.17	\$ 69.28
Part Number	T066997PP	T066997PP	T066997PP	T066998PP	T066999PP	T067000PP	T067001PP	T067002PP	T067003PP	T067004PP

PTFE Bonnet Gasket


Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 0.86	\$ 0.86	\$ 0.86	\$ 0.86	\$ 2.06	\$ 2.59	\$ 3.24	\$ 3.90	\$ 8.87	\$ 15.27
Part Number	T066965PP	T066965PP	T066965PP	T066966PP	T066967PP	T066968PP	T066969PP	T066970PP	T066971PP	T066972PP

NPT Plug

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 2.06	\$ 2.06	\$ 2.06	\$ 2.06	\$ 2.92	\$ 5.95	\$ 5.95	\$ 6.06	\$ 13.42	\$ 22.08
Part Number	T067044PP	T067044PP	T067044PP	T067045PP	T067045PP	E177050FC	E177050FC	E177100FC	E177150FC	E177200FC

⚠ **WARNING:** Cancer and Reproductive Harm – www.P65Warnings.ca.gov.

IRON REPLACEMENT PARTS



T-751-A — 20 Mesh (1/4" - 2"), 1/16" Perforated (2 1/2" - 3") Stainless Steel Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 3.90	\$ 3.90	\$ 3.90	\$ 5.20	\$ 5.20	\$ 5.20	\$ 6.50	\$ 7.69	\$ 43.19	\$ 57.15
Part Number	RG60009	RG60010	RG60011	RG60012	RG60013	RG60014	RG60015	RG60016	RG60017	RG60018



F-721-A — 1/16" Perforated (2" - 4"), 1/8" Perforated (5" - 16") Stainless Steel Screens

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"	14"	16"
List Price	\$ 34.42	\$ 44.49	\$ 50.87	\$ 80.00	\$ 157.50	\$ 258.70	\$ 376.70	\$ 546.00	\$ 789.00	\$ 1,243.00	\$ 1,714.00
Part Number	RG60019	RG60020	RG60021	RG60022	RG60023	RG60024	RG60025	RG60026	RG60027	RG60028	RG60029

T-751-A — Metal-Filled Graphite Bonnet Gasket

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 3.90	\$ 3.90	\$ 3.90	\$ 3.90	\$ 3.90	\$ 5.20	\$ 5.20	\$ 6.50	\$ 8.99	\$ 8.99
Part Number	RG60030	RG60031	RG60032	RG60033	RG60034	RG60035	RG60036	RG60037	RG60038	RG60039

F-721-A — Metal-Filled Graphite Bonnet Gasket

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
List Price	\$ 7.69	\$ 8.99	\$ 10.28	\$ 12.88	\$ 17.86	\$ 25.55	\$ 27.93	\$ 31.83	\$ 40.59
Part Number	RG60040	RG60041	RG60042	RG60043	RG60044	RG60045	RG60046	RG60047	RG60048

T-751-A — Iron NPT Plug

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 6.50	\$ 6.50	\$ 6.50	\$ 6.50	\$ 6.50	\$ 7.69	\$ 7.69	\$ 8.99	\$ 8.99	\$ 14.07
Part Number	RG60001	RG60001	RG60001	RG60002	RG60002	RG60004	RG60004	RG60005	RG60005	RG60006

F-721-A — Iron NPT Plug

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
List Price	\$ 6.50	\$ 8.99	\$ 8.99	\$ 15.27	\$ 21.65	\$ 21.65	\$ 21.65	\$ 21.65	\$ 21.65
Part Number	RG60003	RG60005	RG60005	RG60007	RG60008	RG60008	RG60008	RG60008	RG60008

⚠ **WARNING:** Cancer and Reproductive Harm – www.P65Warnings.ca.gov.

NIBCO®

AHEAD OF THE FLOW®

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
 ELKHART, IN 46516-4740
 USA

DOMESTIC CUSTOMER SERVICE
 PHONE: 800.234.0227
 FAX: 800.234.0557

TECHNICAL SERVICE
 PHONE: 888.446.4226
 FAX: 888.336.4226

INTERNATIONAL OFFICE
 PHONE: +1/574.295.3327
 FAX: +1/574.295.3455