



List Prices subject to change without notice  
Visit our website for the most current information.

### BRONZE Y-STRAINER — SOLDER END W/PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>S-221-A</b> Class 125 20 Mesh Screen w/Plug	List Price	N/A	N/A	\$ 74.06	\$ 88.19	\$ 123.40	\$ 180.00	\$ 207.40	\$ 335.00	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279927	279934	279941	279958	279965	279972	—	—
<b>S-222-A</b> Class 125 Perforated Stainless Steel w/Plug	List Price	N/A	N/A	\$ 84.66	\$ 98.67	\$ 134.00	\$ 200.50	\$ 227.90	\$ 371.50	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280091	280107	280169	280176	280183	280190	—	—



### BRONZE Y-STRAINER — SOLDER END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>S-221-B</b> Class 125 20 Mesh Screen w/Solid Cap	List Price	N/A	N/A	\$ 74.06	\$ 88.19	\$ 124.50	\$ 177.70	\$ 206.20	\$ 332.60	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279989	279996	280008	280060	280077	280084	—	—
<b>S-222-B</b> Class 125 Perforated Stainless Steel w/Solid Cap	List Price	N/A	N/A	\$ 79.99	\$ 94.00	\$ 131.70	\$ 194.80	\$ 219.90	\$ 361.10	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280206	280213	280251	280268	280275	280282	—	—



### BRONZE Y-STRAINER — THREADED END W/ PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>T-221-A</b> Class 125 20 Mesh Screen w/Plug	List Price	\$ 71.67	\$ 71.67	\$ 71.67	\$ 97.53	\$ 124.50	\$ 173.90	\$ 208.50	\$ 358.80	\$ 781.00	\$ 1,066.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.96
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280299	280305	280312	280350	280367	280374	280381	280398	280442	280459
<b>T-222-A</b> Class 125 Perforated Stainless Steel w/Plug	List Price	\$ 74.06	\$ 74.06	\$ 74.06	\$ 104.60	\$ 132.70	\$ 188.00	\$ 221.00	\$ 384.00	\$ 836.00	\$ 1,142.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280619	280626	280633	280640	280657	280664	280671	280688	280695	280701

WARNING: Cancer and Reproductive Harm – www.P65Warnings.ca.gov.

**NIBCO**  
AHEAD OF THE FLOW®

**NIBCO INC.**  
**WORLD HEADQUARTERS**  
**WEB: www.nibco.com**

1516 MIDDLEBURY STREET  
ELKHART, IN 46516-4740  
USA

DOMESTIC CUSTOMER SERVICE  
PHONE: 800.234.0227  
FAX: 800.234.0557

TECHNICAL SERVICE  
PHONE: 888.446.4226  
FAX: 888.336.4226

INTERNATIONAL OFFICE  
PHONE: +1/574.295.3327  
FAX: +1/574.295.3455



### BRONZE Y-STRAINER — THREADED END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>T-221-B</b> Class 125 20 Mesh Screen w/Solid Cap	List Price	\$ 68.13	\$ 68.13	\$ 68.13	\$ 94.00	\$ 123.40	\$ 171.70	\$ 206.20	\$ 354.30	\$ 774.00	\$ 1,056.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280466	280473	280480	280497	280541	280558	280565	280572	280596	280602
Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>T-222-B</b> Class 125 Perforated Stainless Steel w/Solid Cap	List Price	\$ 71.67	\$ 71.67	\$ 71.67	\$ 101.10	\$ 126.80	\$ 180.00	\$ 213.00	\$ 368.00	\$ 805.00	\$ 1,092.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280848	280855	280862	280879	280886	280893	280909	281029	281036	281043



### IRON Y-STRAINER — THREADED END

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>T-751-A</b> Class 250 20 Mesh Screen w/Plug	List Price	\$ 28.14	\$ 28.14	\$ 28.14	\$ 41.48	\$ 54.81	\$ 71.21	\$ 98.44	\$ 150.30	\$ 298.50	\$ 410.20
	Unit Wgt.	1.39	1.39	1.39	2.20	3.08	5.06	7.70	12.54	24.42	29.26
	Case Qty.	10	10	10	10	8	6	4	3	1	1
	UPC 039923-	308498	308511	308535	308559	308573	308580	308597	308610	308634	308658



### IRON Y-STRAINER — FLANGED

Fig. No.	Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
<b>F-721-A</b> Class 125 Perforated Screen w/Plug	List Price	\$ 311.00	\$ 338.40	\$ 396.50	\$ 601.00	\$ 1,094.00	\$ 1,357.00	\$ 2,401.00	\$ 4,447.00	\$ 6,347.00
	Unit Wgt.	18.04	32.56	37.84	67.10	94.60	136.62	270.60	374	605
	Case Qty.	1	1	1	1	1	1	1	1	1
	UPC 039923-	308672	308696	308702	308719	308733	308757	308771	308795	308801




### IRON Y-STRAINER — FLANGED

Fig. No.	Size	14"	16"
<b>F-721-A</b> Class 125 Perforated Screen w/Plug	List Price	\$ 13,765.00	\$ 19,396.00
	Box Qty	10	10
	Unit Wgt.	863	1380
	Case Qty.	1	1
	UPC 039923-	310415	310422

**WARNING:** Cancer and Reproductive Harm – [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## BRONZE REPLACEMENT PARTS



### 20 Mesh Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 21.76	\$ 21.76	\$ 21.76	\$ 21.76	\$ 25.99	\$ 31.79	\$ 36.11	\$ 62.32	\$ 27.58	\$ 54.91
Part Number	T066957PP	T066957PP	T066957PP	T066958PP	T066959PP	T066960PP	T066961PP	T066962PP	T066963PP	T066964PP



### Perforated Stainless Steel Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 21.76	\$ 21.76	\$ 21.76	\$ 20.28	\$ 25.06	\$ 24.61	\$ 30.30	\$ 39.08	\$ 54.91	\$ 72.92
Part Number	T066997PP	T066997PP	T066997PP	T066998PP	T066999PP	T067000PP	T067001PP	T067002PP	T067003PP	T067004PP

### PTFE Bonnet Gasket


Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 0.91	\$ 0.91	\$ 0.91	\$ 0.91	\$ 2.17	\$ 2.73	\$ 3.41	\$ 4.11	\$ 9.34	\$ 16.07
Part Number	T066965PP	T066965PP	T066965PP	T066966PP	T066967PP	T066968PP	T066969PP	T066970PP	T066971PP	T066972PP

### NPT Plug

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 2.17	\$ 2.17	\$ 2.17	\$ 2.17	\$ 3.07	\$ 6.26	\$ 6.26	\$ 6.38	\$ 14.13	\$ 23.24
Part Number	T067044PP	T067044PP	T067044PP	T067045PP	T067045PP	E177050FC	E177050FC	E177100FC	E177150FC	E177200FC

⚠ **WARNING:** Cancer and Reproductive Harm – [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## IRON REPLACEMENT PARTS



### T-751-A — 20 Mesh (1/4" - 2"), 1/16" Perforated (2 1/2" - 3") Stainless Steel Screens

<b>Size</b>	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>List Price</b>	\$ 4.11	\$ 4.11	\$ 4.11	\$ 5.47	\$ 5.47	\$ 5.47	\$ 6.84	\$ 8.09	\$ 45.46	\$ 60.16
<b>Part Number</b>	RG60009	RG60010	RG60011	RG60012	RG60013	RG60014	RG60015	RG60016	RG60017	RG60018



### F-721-A — 1/16" Perforated (2" - 4"), 1/8" Perforated (5" - 16") Stainless Steel Screens

<b>Size</b>	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"	14"	16"
<b>List Price</b>	\$ 36.23	\$ 46.83	\$ 53.55	\$ 84.21	\$ 165.80	\$ 272.30	\$ 396.50	\$ 575.00	\$ 831.00	\$ 1,308.00	\$ 1,804.00
<b>Part Number</b>	RG60019	RG60020	RG60021	RG60022	RG60023	RG60024	RG60025	RG60026	RG60027	RG60028	RG60029

### T-751-A — Metal-Filled Graphite Bonnet Gasket

<b>Size</b>	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>List Price</b>	\$ 4.11	\$ 4.11	\$ 4.11	\$ 4.11	\$ 4.11	\$ 5.47	\$ 5.47	\$ 6.84	\$ 9.46	\$ 9.46
<b>Part Number</b>	RG60030	RG60031	RG60032	RG60033	RG60034	RG60035	RG60036	RG60037	RG60038	RG60039

### F-721-A — Metal-Filled Graphite Bonnet Gasket

<b>Size</b>	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
<b>List Price</b>	\$ 8.09	\$ 9.46	\$ 10.82	\$ 13.56	\$ 18.80	\$ 26.89	\$ 29.40	\$ 33.50	\$ 42.72
<b>Part Number</b>	RG60040	RG60041	RG60042	RG60043	RG60044	RG60045	RG60046	RG60047	RG60048

### T-751-A — Iron NPT Plug

<b>Size</b>	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
<b>List Price</b>	\$ 6.84	\$ 6.84	\$ 6.84	\$ 6.84	\$ 6.84	\$ 8.09	\$ 8.09	\$ 9.46	\$ 9.46	\$ 14.81
<b>Part Number</b>	RG60001	RG60001	RG60001	RG60002	RG60002	RG60004	RG60004	RG60005	RG60005	RG60006

### F-721-A — Iron NPT Plug

<b>Size</b>	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
<b>List Price</b>	\$ 6.84	\$ 9.46	\$ 9.46	\$ 16.07	\$ 22.79	\$ 22.79	\$ 22.79	\$ 22.79	\$ 22.79
<b>Part Number</b>	RG60003	RG60005	RG60005	RG60007	RG60008	RG60008	RG60008	RG60008	RG60008

⚠ **WARNING:** Cancer and Reproductive Harm – [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**NIBCO**<sup>®</sup>  
AHEAD OF THE FLOW<sup>®</sup>

**NIBCO INC.**  
**WORLD HEADQUARTERS**  
**WEB:** [www.nibco.com](http://www.nibco.com)

1516 MIDDLEBURY STREET  
ELKHART, IN 46516-4740  
USA

DOMESTIC CUSTOMER SERVICE  
PHONE: 800.234.0227  
FAX: 800.234.0557

TECHNICAL SERVICE  
PHONE: 888.446.4226  
FAX: 888.336.4226

INTERNATIONAL OFFICE  
PHONE: +1/574.295.3327  
FAX: +1/574.295.3455